

Features

- Functions as a diverter or selector valve
- All materials comply with FDA and USDA requirements
- Pneumatic actuator with integral manual override
- Tri-Clamp ends for hygienic connections
- Dyneon® TF-1641 (PTFE) FDA approved ball seats and cavity fillers
- Triple PTFE/Viton® high cycle live loaded stem seal packing
- Highly polished internals and end caps with 8-12 Ra finish
- Rack and pinion quarter turn (90°) rotation
- Spring Return or Double Acting Actuators
- Type IP67 weatherproof actuator
- Variable open/close stroke setting
- ATEX approved
- Highly visible valve position indicator
- Actuator factory lubricated for normal lifetime

Applications

Pneumatic/manual actuated sanitary 3-way ball valves are typically used for food, beverage, pharmaceutical, personal care, and pet care applications where sanitary construction is required, as well as for utility and process applications where quick clamp connections are beneficial. The de-clutch option can be used for manual operation or to set a stop limit for opening or closing. Cycle times approx. 1 to 3 seconds per 90° rotation.


Operation

Double acting actuators require air pressure to open and air pressure to close. Spring return actuators require air pressure to open and utilize springs to close for failsafe operation. Pulling the handwheel détente pin allows manual operation of the valve via the handwheel. Re-engaging the détente pin mid-stroke creates a partial stroke position, ie the automatic stroke begins/ends at the locked handwheel position. Rotating the handwheel counterclockwise rotates the output drive counterclockwise when viewed from the top.

Pilot Air should be filtered, dry or lubricated.

Construction

Valve Body	ASTM 316 stainless steel
Ball/Stem	ASTM 316 stainless steel
Ball Seats/ Cavity Filler	Dyneon® PTFE
Stem Seals	PTFE/ Viton®
Actuator Seals	NBR (Buna-N)
Actuator Body	Extruded aluminium- 35 micron anodizing, 40 micron polyester coated end covers
Position Indicator	Glass filled Polyamide
Fasteners	Stainless Steel



Description

Valworx heavy duty pneumatic/manual combination actuator features hard anodized aluminum enclosure, type IP67. Actuators are available in double acting and spring return models. Sanitary 3-way L-port flow pattern ball valve has four Dyneon® PTFE ball seats, allowing for full pressure at any port. Adjustable live loaded stem seal packing helps compensate for wear, pressure and temperature fluctuations, extending the cycle life of the valve. Blow-out proof stem. Cavity fillers avoid media entrapment and quick clamp end connections allow for easy cleaning. Standard Namur mounting pads for optional accessory configuration switches, pilot valves and valve positioners. Rotation adjustment +5° at the 0° and 90° positions. The integral handwheel is used for manual operation and setting a limit stop.

Approvals- Actuators


- CE Declaration of conformity
- EN ISO 12100:2010
- EN ISO 4414:2010
- ISO5211/ DIN3337 valve mounting
- Namur VDI/VDE 3845 accessory mounting
- ATEX



Standards- Valves

- Design: API 608
- Testing: API 598
- Threaded Connection: ASME B1.20.1 (NPT)/ ISO 228-1/ BS21
- Pressure/Temperature Rating: ASME B16.34
- Marking: MSS SP-25
- CE conformance- EPED 2014/68/UE

Features



Pressure Rating

Shell Pressure Rating (Max)*: 1000 PSI @ 120°F (1/2" to 2"),
600 PSI (2 1/2" to 3")

*See P/T Chart

Pilot Air Pressure– Double Acting: 29-120 PSI (2-8 Bar)

Pilot Air Pressure– Spring Return: 87-120 PSI (6-8 Bar)

Temperature Rating

Valve Temperature Rating: -4° to 356° F (-20 to 180°C)

Actuator Temperature Rating: -4 to 176° F (-20 to 80°C)

*See P/T Chart

Optional Accessories

DMS: Direct Mount Solenoid
- pilot to electrically operate the ball valve
VPS: Valve Position Switches
- limit switches to confirm valve position
PVP: Pneumatic Valve Positioner
- position the ball with 4-20mA
HTB: High Temperature Bracket
- increases media working temperature
Lock out/Tag out device
Inline mounting

Specifications (English units)

Stock Number	Pipe Size (inch)	Tri-Clamp Size (inch)	Cv Flow Factor	Shell Pressure Max.(PSI)*	Cycle Time /90° (seconds)	Air Volume (standard cubic inches)	Pilot Air Port (NPT)
SANITARY L-PORT VALVE WITH PNEUMATIC/MANUAL SPRING RETURN ACTUATOR							
575600	1/2	3/4	4.3	1000	1/1	24.4	1/4
575601	3/4	3/4	10.4	1000	1/1	24.4	1/4
575602	1	1-1/2	17.3	1000	2/1	42.7	1/4
575603	1-1/2	1-1/2	43.3	1000	3/1	91.5	1/4
575604	2	2	77.9	1000	3/1	91.5	1/4
SANITARY L-PORT VALVE WITH PNEUMATIC/MANUAL DOUBLE ACTING ACTUATOR							
575500	1/2	3/4	4.3	1000	1/1	18.3	1/4
575501	3/4	3/4	10.4	1000	1/1	18.3	1/4
575502	1	1-1/2	17.3	1000	1/1	18.3	1/4
575503	1-1/2	1-1/2	43.3	1000	2/2	24.4	1/4
575504	2	2	77.9	1000	2/2	54.9	1/4

Cv = The GPM of water at 60° F that will pass through the valve with 1 PSI pressure drop


* Pressure @ -4° to 356° F (reduced pressure at higher temperatures—see P/T chart)

• Torque at 1000 PSI and 72°F

Pressure/Temperature Chart (PSI/°F)

Standard Units

Temp °F	-4	120	356
Pressure	1000	1000	0



Specifications (Metric units)


Stock Number	Pipe Size (mm)	Tri-Clamp Size (inch)	Kv Flow Factor	Shell Pressure Max.(Bar)*	Cycle Time/90° (seconds)	Air Volume (standard liters)	Pilot Air Port (NPT)
SANITARY L-PORT VALVE WITH PNEUMATIC/MANUAL SPRING RETURN ACTUATOR							
575600	12.7	3/4	5.0	69	1/1	0.4	1/4
575601	19.1	3/4	12.0	69	1/1	0.4	1/4
575602	25.4	1-1/2	20.0	69	2/1	0.7	1/4
575603	38.1	1-1/2	50.0	69	3/1	1.5	1/4
575604	50.8	2	90.0	69	3/1	1.5	1/4
SANITARY L-PORT VALVE WITH PNEUMATIC/MANUAL DOUBLE ACTING ACTUATOR							
575500	12.7	3/4	5.0	69	1/1	0.3	1/4
575501	19.1	3/4	12.0	69	1/1	0.3	1/4
575502	25.4	1-1/2	20.0	69	1/1	0.3	1/4
575503	38.1	1-1/2	50.0	69	2/2	0.4	1/4
575504	50.8	2	90.0	69	2/2	0.9	1/4

* Pressure range @ -20° to 180° C (reduced pressure for higher temperatures—see P/T chart)


Pressure/Temperature Chart (Bar/°C)

Metric Units

Temp °C	-20	49	180
Pressure	69	69	0




Dimensions: Spring Return



Pipe Size		A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	Weight
1/2	inch	9.2	3.3	8.5	2.8	2.4	9.5	3.3	2.3	4.2	3.7	7.7	2.0	0.3	0.4	1.2	4.6	14.6 lb
	mm	233.0	83.8	215.9	72.0	60.0	241.3	85.0	59.0	106.7	93.5	195.0	50.0	9.0	9.4	30.0	118.0	6.6 kg
3/4	inch	9.2	3.3	8.6	2.8	2.4	9.6	3.3	2.6	4.3	3.9	7.7	2.0	0.3	0.6	1.2	5.0	15.3 lb
	mm	233.0	83.8	218.4	72.0	60.0	243.8	85.0	64.9	109.2	97.8	195.0	50.0	9.0	15.8	30.0	127.0	6.9 kg
1	inch	9.6	3.6	9.4	3.1	2.4	10.6	3.5	3.0	4.7	4.6	7.1	2.0	0.3	0.9	1.2	6.0	19.0 lb
	mm	244.0	91.4	238.8	80.0	60.0	269.4	89.0	76.2	119.4	117.2	180.0	50.0	9.0	22.2	30.0	152.4	8.6 kg
1-1/2	inch	13.4	5.2	11.3	3.9	3.1	12.9	4.3	3.5	5.9	5.5	9.8	2.8	0.3	1.4	1.4	6.9	36.1 lb
	mm	341.0	132.1	287.0	98.0	80.0	327.7	109.0	88.8	149.9	138.5	250.0	70.0	9.0	35.0	35.0	175.0	16.4 kg
2	inch	13.4	5.2	11.7	3.9	3.1	13.7	4.3	3.8	6.3	6.3	9.8	2.8	0.3	1.9	1.4	7.5	43.5 lb
	mm	341.0	132.1	297.2	98.0	80.0	348.0	109.0	96.3	160.0	160.0	250.0	70.0	9.0	47.6	35.0	190.0	19.8 kg

Dimensions: Double Acting



Pipe Size		A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	Weight
1/2	inch	8.3	3.1	7.8	2.6	2.4	8.8	2.9	2.3	4.2	3.7	7.1	2.0	0.3	0.4	1.2	4.6	10.4 lb
	mm	211.0	78.7	187.2	65.0	60.0	223.5	74.0	59.0	106.7	93.5	180.0	50.0	9.0	9.4	30.0	118.0	4.7 kg
3/4	inch	8.3	3.1	7.9	2.6	2.4	8.9	2.9	2.6	4.3	3.9	7.1	2.0	0.3	0.6	1.2	5.0	11.3 lb
	mm	211.0	78.7	200.7	65.0	60.0	226.1	74.0	64.9	109.2	97.8	180.0	50.0	9.0	15.8	30.0	127.0	5.1 kg
1	inch	8.3	3.1	8.3	2.6	2.4	9.5	2.9	3.0	4.7	4.6	7.1	2.0	0.3	0.9	1.2	6.0	13.7 lb
	mm	211.0	78.7	210.8	65.0	60.0	241.3	74.0	76.2	119.4	117.2	180.0	50.0	9.0	22.2	30.0	152.4	6.2 kg
1-1/2	inch	9.2	3.3	10.2	2.8	3.1	11.8	3.3	3.5	5.9	5.5	7.7	2.8	0.3	1.4	1.4	6.9	23.3 lb
	mm	233.0	83.8	259.1	72.0	80.0	299.7	85.0	88.8	149.9	138.5	195.0	70.0	9.0	35.0	35.0	175.0	10.6 kg
2	inch	10.7	4.2	11.4	3.1	3.1	13.4	4.0	3.8	6.3	6.3	7.7	2.8	0.3	1.9	1.4	7.5	32.0 lb
	mm	271.8	106.7	289.6	80.0	80.0	340.4	101.6	96.3	160.0	160.0	195.0	70.0	9.0	47.6	35.0	190.0	14.5 kg